



LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

## Caden LED Pendant CADP Series

### Features

Luminous cylinder with a white acrylic diffuser.  
Available in three lengths. Includes a 9 ft. adjustable cord.  
Product can be used over receptions desks, restaurants, and in public spaces.  
This fixture mounts to a standard junction box (not included).

### Construction

Metal housing and canopy.  
The canopy fits over a standard junction box.  
Power supply connections must be made inside a junction box (not included).

### Finish

Satin nickel, black or satin brass\* finish.

### Diffuser

White acrylic diffuser.

### Electrical

Input 120-277 VAC 60 HZ.  
Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers.  
TRIAC and ELV dimming only at 120VAC.

### LED

Integrated LED modules capable of producing:  
25W, 2036 delivered lumens  
29W, 2665 delivered lumens  
34W, 2946 delivered lumens  
3000K (CCT). Rated for 50,000 Hrs., 90 CRI.

### Certification

All fixtures are cETLus listed for indoor damp locations.

### Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 year from date of purchase.

**Specifications and dimensions**  
subject to change without notice.

## Ordering Information:

Satin Nickel	Black	Satin Brass*	LED	Delivered Lumens	CCT	Pendant DIA.	H
CADP24L30UDSN	CADP24L30UDBK	CADP24L30UDSB	25W	2036	3000K	2-1/2"	24"
CADP36L30UDSN	CADP36L30UDBK	CADP36L30UDSB	29W	2665	3000K	2-1/2"	36"
CADP48L30UDSN	CADP48L30UDBK	CADP48L30UDSB	34W	2946	3000K	2-1/2"	48"

\*Special Order - consult factory for MOQ and lead time.

