



LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

Cass LED Vanity CSSV Series

Features

This vanity features four-sided illumination with a white acrylic diffuser. Provides lighting in residential, commercial and hospitality applications. This fixture mounts to a standard junction box (not included).



Construction

Extruded aluminum housing. The canopy fits over a standard junction box. Power supply connections must be made inside a junction box (not included).

Finish

Black, Gold, or Satin Nickel finish.

Diffuser

White acrylic diffuser.

Electrical

Input 120 VAC 60 HZ.
Compatible with TRIAC and ELV dimmers.

LED

Integrated LED modules capable of producing:
24W = 2400 source lumens, 1700 delivered lumens
38W = 4000 source lumens, 2475 delivered lumens
3000K (CCT). Rated for 50,000 Hrs., 90 CRI.

Certification

All fixtures are cETLus listed for indoor damp locations.
ADA compliant.
Title 24/JA8 compliant.

Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 year from date of purchase.

Specifications and dimensions
subject to change without notice.



BK
24"



GD
24"



Ordering Information:

Black	Gold	Satin Nickel	LED	Source Lumens	Delivered Lumens	CCT	H	W	D
CSSV2404L30D1BK	CSSV2404L30D1GD	CSSV2404L30D1SN	24W	2400	1700	3000K	24"	5"	4"
CSSV3804L30D1BK	CSSV3804L30D1GD	CSSV3804L30D1SN	38W	4000	2475	3000K	36"	5"	4"