



Evanston LED Pendant EVNP Series

Features

Decorative cream linen pendant with satin nickel accent detail.
Suspended with a 3 ft. adjustable rigid stem expandable up to 9 ft.
Product can be used over receptions desks, restaurants, and in public spaces.
Canopy mounts to a standard junction box (not included).

Construction

Metal housing and canopy.
The canopy fits over a standard junction box.
Power supply connections must be made inside a junction box (not included).

Finish

Satin nickel.

Electrical

Input 120-277 VAC 60 HZ.
Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers.
TRIAC and ELV dimming only at 120VAC.

LED

Integrated LED modules capable of producing:
42W = 3200 lumens
Adjustable Choice 3000K, 3500K, 4000K (CCT).
Rated for 50,000 Hrs., 90 CRI.

Certification

cETLus listed for indoor damp locations
Title 24/JA8 Compliant

Options

Additional stems sold separately.

Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 year from date of purchase.

Specifications and dimensions
subject to change without notice.

Ordering Information:

Satin Nickel	LED	Source Lumens	Adjustable CCT	DIA.	H
EVNP2532LAJUDSN	42W	3200	3000K/3500K/4000K	25"	12"

LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		



3in1 color temperature
3000K/3500K/4000K

