



LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

Lake Medium Base Ceiling LAKF Series

Features

This ceiling mount features a laser cut design with a white acrylic diffuser. For use in kitchen, dining, foyers or anywhere general lighting is needed. Provides lighting in residential, commercial and hospitality applications. This fixture mounts to a standard junction box (not included).

Construction

Extruded aluminum housing. The canopy fits over a standard junction box. Power supply connections must be made inside a junction box (not included).

Finish

Black, Gold or Painted Nickel finish.

Diffuser

White acrylic diffuser.

Electrical

120V medium base sockets.

Lamping

For use with 100W equivalent LED bulb.
(3) or (4) 25W Max medium base bulbs (lamps not included).

Certification

All fixtures are cETLus listed for indoor damp locations.

Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 2 years from date of purchase.

**Specifications and dimensions
subject to change without notice.**



GD
16"



NP
24"



BK
30"



Ordering Information:

Black	Gold	Painted Nickel	Qty.	Lamp	DIA.	D
LAKF16MGBK	LAKF16MBGD	LAKF16MBNP	3	25W (MAX)	16"	4"
LAKF20MGBK	LAKF20MBGD	LAKF20MBNP	3	25W (MAX)	20"	5"
LAKF24MGBK	LAKF24MBGD	LAKF24MBNP	3	25W (MAX)	24"	6"
LAKF30MGBK	LAKF30MBGD	LAKF30MBNP	4	25W (MAX)	30"	7"