



LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

## Montclair Medium Base Flush Mount MCF Series

### Features

This modern step drum design provides a dramatic look and features Lumafuse™ laminated fabric/acrylic shade. White bottom acrylic diffuser disperses the light. Ideal use in kitchens, hallways, and anywhere general lighting is needed. Provides lighting in residential, commercial and hospitality applications. Fixture mounts to standard junction box (not included).

### Construction

Special laminated fabric on acrylic material with recessed center and white bottom diffuser. Back pan is made from 22-gauge stamped steel and painted in lighting grade white. Standard mounting holes and hardware included. Power supply connections must be made inside a junction box (not included).

### Finish

Satin Nickel finish.

### Diffuser

Utilizing Lumafuse™ laminated fabric to acrylic in Black or Grey. Matte white acrylic bottom diffuser.

### Electrical

120V medium base sockets.

### Lamping

For use with 100W equivalent LED bulb. (2), (3) or (4) 25W Max medium base bulbs (lamps not included).

### Certification

All fixtures are cETLus listed for indoor damp locations.

### Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 year from date of purchase.

**Specifications and dimensions**  
subject to change without notice.

## Ordering Information:

### FLUSH MOUNT

Black	Grey	Qty.	Lamp	DIA.	D
MCF1214MBBK	MCF1214MB-GY	2	25W (MAX)	12-1/4"	3-3/4"
MCF1524MB-BK	MCF1524MB-GY	3	25W (MAX)	15"	4-3/4"
MCF1932MB-BK	MCF1932MB-GY	3	25W (MAX)	19-1/4"	5-1/2"
MCF2432MB-BK	MCF2432MB-GY	3	25W (MAX)	24"	7-1/2"
MCF3044MB-BK	MCF3044MB-GY	4	25W (MAX)	30"	9-1/2"

### SEMI-FLUSH MOUNT

Black	Grey	Qty.	Lamp	DIA.	D
MCF1214MB-BKSF	MCF1214MB-GYSF	2	25W (MAX)	12-1/4"	9"
MCF1524MB-BKSF	MCF1524MB-GYSF	3	25W (MAX)	15"	10"
MCF1932MB-BKSF	MCF1932MB-GYSF	3	25W (MAX)	19-1/4"	10-3/4"
MCF2432MB-BKSF	MCF2432MB-GYSF	3	25W (MAX)	24"	12-3/4"
MCF3044MB-BKSF	MCF3044MB-GYSF	4	25W (MAX)	30"	14-3/4"



Black



Grey  
Semi-Flush

