



LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

## Randolph LED Overbed RAB Series

### Features

Contemporary LED wall mount senior care overbed light with a beautiful combination of finish and shade materials. White acrylic top and bottom diffuser. Provides both ambient and task light with a four way pull switch, standard (120 volt only).



### Construction

The wiring channel is formed from 22-gauge steel and is provided with mounting slots and wiring access. An internal divider provides separate lamp compartments for controlled up light and down light. Fixture can mount horizontally only. Power connections can be made in the fixture wiring channel or in a standard junction box (not included).

### Finish

Faux metal finish in Satin Nickel or Oil-Rubbed Bronze.

### Diffuser

LumaFuse™ double laminated fabric/acrylic. 0.110" thick fabric is available in Jute or Linen White. Standard top and bottom diffuser.

### Electrical

Input 120VAC / 60 Hz  
Not compatible with dimmers. Integrated four position pull switch (on up, on down, on both, all off) and single pull switch for nightlight.

### LED

Integrated LED modules capable of producing:  
60W = 4050 source lumens  
80W = 5400 source lumens  
Rated for 50,000 hours, 3000K (CCT), 90 CRI.  
Provides 50 footcandles of reading light over bed.

### Certification

All fixtures are cETLus listed for indoor damp locations.  
ADA

### Options (Consult Factory)

120-277V universal voltage available without switch and nightlight.

### Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 years from date of purchase.

**Specifications and dimensions**  
subject to change without notice.

### Ordering Information:

Jute		Jute		LED	Source Lumens	CCT	L	H	D
Satin Nickel	Oil-Rubbed Bronze	Oil-Rubbed Bronze	Oil-Rubbed Bronze						
RAB384000L30ENSN-JT	RAB384000L30ENRB-JT	60W	1350 up/2700 down	3000K	38"	4-7/8"	4"		
RAB505400L30ENSN-JT	RAB505400L30ENRB-JT	80W	1800 up/3600 down	3000K	50"	4-7/8"	4"		
Linen White		Linen White		LED	Source Lumens	CCT	L	H	D
Satin Nickel	Oil-Rubbed Bronze	Oil-Rubbed Bronze	Oil-Rubbed Bronze						
RAB384000L30ENSN-LW	RAB384000L30ENRB-LW	60W	1350 up/2700 down	3000K	38"	4-7/8"	4"		
RAB505400L30ENSN-LW	RAB505400L30ENRB-LW	80W	1800 up/3600 down	3000K	50"	4-7/8"	4"		

