



## Sheridan LED Sconce SHS081807LAJUDACLA

### Features

Transitional arm light wall mount sconce is ADA compliant and fully enclosed with a top and bottom diffuser. Fixture mounts to junction box behind the shade (not included).

### Construction

Back plate is die formed of 20-gauge steel. Standard mounting holes and hardware are included. Power supply connections can be made inside a junction box (not included) or inside the ballast compartment. The arms are tapered cast aluminum and require assembly to the backplate and wall.

### Finish

Backplate is finished in lighting grade white baked gloss enamel paint. Cast arm is finished in anodized champagne or a plated satin nickel.

### Diffuser

Diffuser is a hard backed white linen acrylic (LA). Shade mounts to back plate with two screws. Top and bottom diffusers are .100" matte white acrylic.

### Electrical

This unit is direct wired with a constant current LED driver rated for 120-277V. Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers. TRIAC and ELV dimming only at 120VAC.

### Lamping

Fixture includes LED modules producing:  
7W = 700 source lumens  
3000K (CCT).  
Rated for 50,000 Hrs., 90 CRI

### Certification

All fixtures are cETLus listed for damp locations.

### Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 years from date of purchase.

**Specifications and dimensions  
subject to change without notice.**

## Ordering Information:

Linen Acrylic Shade

Champagne	LED	Lumens	CCT	H	W	D
SHS061807LAJUDACLA	7W	700	3000K	18-1/2"	6-1/8"	4"

LOCATION	DATE
PREPARED BY	QUANTITY
COMMENTS	FIXTURE TYPE
CATALOG NUMBER	

