



LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		



Studio LED Flush Mount STDF Series

Features

Studio LED flush mount fixture provides beauty and light to any room. Ideal use in kitchens, hallways, and anywhere general lighting is needed. Provides lighting in residential, commercial and hospitality applications. Fixture mounts to standard junction box (not included).

Construction

Metal housing with a clear acrylic ring and white acrylic diffuser. Standard mounting holes and hardware included. The canopy fits over a standard junction box. Power supply connections must be made inside a junction box (not included).

Finish

Polished Chrome, Satin Brass or Black finished ring.

Diffuser

Clear acrylic side diffuser with a white acrylic bottom diffuser.

Electrical

Input 120 VAC / 60HZ.
Compatible with TRIAC and ELV dimmers.

LED

Integrated LED modules capable of producing:
20W = 1200 delivered lumens
25W = 1500 delivered lumens
Adjustable Choice 2700K, 3000K, 3500K, 4000K, 5000K (CCT).
Rated for 50,000 Hrs., 90 CRI.

Certification

All fixtures are cETLus listed for indoor damp locations.
Title 24/JA8 Compliant

Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 years from date of purchase.
subject to change without notice.

Specifications and dimensions



Ordering Information:

Black	Polished Chrome	Satin Brass	LED	Delivered Lumens	Adjustable CCT	DIA.	D
STDF12LAJD1BK	STDF12LAJD1PC	STDF12LAJD1SB	20W	1200	2700K/2700K/3000K/3500K/4000K	12"	3-1/4"
STDF16LAJD1BK	STDF16LAJD1PC	STDF16LAJD1SB	25W	1500	2700K/2700K/3000K/3500K/4000K	15-1/2"	3-1/4"