



LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

Outdoor LED Flood Light TPDW70050LBK, TPDW1300L50BK, TPDW4000L50BK



Features

All purpose long lasting energy saving LED flood light. An excellent alternative solution to incandescent fixtures. Ideal use for security and general lighting in outdoor residential, commercial, and hospitality applications. Fixture can be installed to a standard flood light cover plate (not included).

Construction

Housing is made from die-cast aluminum with a durable powder coat. Power supply connections must be made inside a junction box (not included).

Finish

Available in Black finish.

Diffuser

Clear polycarbonate. Replaceable lens is secured to housing with screws.

Electrical

Input 120V VAC / 60 Hz.
Not compatible with dimmers.
Minimum starting temp -4° F/-20° C.

LED

Integrated LED modules capable of producing:
9W = 900 Source Lumens, 790 Delivered Lumens
13.5W = 1500 Source Lumens, 1350 Delivered Lumens
28W = 4000 Source Lumens, 2900 Delivered Lumens
5000K (CCT). Rated for 50,000 Hrs. 80 CRI.

Certification

ETL certified for outdoor wet locations.
Title 24/JA8 Compliant
*ENERGY STAR® Qualified

Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 years from date-of-purchase.

Specifications and dimensions
subject to change without notice.

Ordering Information:

Black	LED	Source Lumens	Delivered Lumens	CCT	H	W	D
TPDW70050LBK*	9W	900	790	5000K	4"	8"	5-7/8"
TPDW1300L50BK	13.5W	1500	1350	5000K	4"	8"	5-7/8"
TPDW4000L50BK	28W	4000	2900	5000K	4"	8"	5-7/8"

