



LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

Glo LED Pendant GLOP Series



Features

Perimeter illumination top and bottom. Includes 9 ft. adjustable cable.
For use in kitchen, dining, foyers or anywhere general lighting is needed.
Provides lighting in residential, commercial and hospitality applications.
This fixture mounts to a standard junction box (not included).

Construction

Extruded aluminum housing. The canopy fits over a standard junction box.
Power supply connections must be made inside a junction box (not included).

Finish

Black, Satin Brass or Satin Nickel finish.

Diffuser

White acrylic diffuser.

Electrical

Input 120 VAC 60 Hz.
Compatible with residential TRIAC and ELV dimmers.

LED

Integrated LED modules capable of producing:
24 in. - 30W = 1400 delivered lumens
36 in. - 40W = 1750 delivered lumens
48 in. - 40W = 2400 delivered lumens
3000K (CCT) rated for 50,000 hrs., 90 CRI.

Certification

All fixtures are cETLus listed for indoor damp locations.
Title 24/JA8 Compliant

Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 years from date of purchase.

Specifications and dimensions

subject to change without notice.



Ordering Information:

Round

Black	Satin Brass	Satin Nickel	LED	Delivered Lumens	CCT	H	DIA.
GLOP24L30D1BK	GLOP24L30D1SB	GLOP24L30D1SN	30W	1400	3000K	1-1/2"	23-3/4"
GLOP36L30D1BK	GLOP36L30D1SB	GLOP36L30D1SN	40W	1750	3000K	1-1/2"	35-1/2"

Linear

Black	Satin Brass	Satin Nickel	LED	Delivered Lumens	CCT	H	L	W
GLOP48L30D1BK	GLOP48L30D1SB	GLOP48L30D1SN	40W	2400	3000K	1-1/4"	47-1/4"	11-3/4"