

Style # 1245-LZ-RD



ironwear

ITEM#: 1245-LZ-RD
 SIZE: MD
 Class 2
 Meets ANSI/ISEA 107-(year)
 100% POLYESTER
 Care Instructions:
 Machine Wash warm, Tumble dry low, Do not bleach, Do not iron, Do not dry clean

Type R
 Class 2
 NOT FR

This garment is not flame resistant as defined by ANSI/ISEA 107-(year) Section 10.5

**RN95108
 MADE IN CHINA**



(Front)



(Back)



(Side)

Features

- > **Description:** 100% polyester mesh safety vest with 2 radio clip holders and 2" reflective tape over contrasting fabric that extends over the shoulders, around the torso and in an H-pattern across the back
- > **Binding:** Hi-vis silver reflective and black polyester
- > **Material:** 100% polyester mesh fabric
- > **Color:** Hi-vis lime
- > **Standard:** ANSI/ISEA 107
- > **Class:** Type R, Class 2
- > **Closure:** Zipper front closure
- > **Tape:** 2" silver reflective tape over 3" hi-vis orange mesh fabric
- > **Pockets:** 11 Pockets - 2 waist pockets with flaps, 2 left chest pockets, 1 upper right chest pocket with 4 pen pockets overtop, 1 inside waist pocket and 1 inside tablet pocket

Measurements

Size	SM	MD	LG	XL	2XL	3XL	4XL	5XL
Width (in)	22	23.5	25	26.5	28	29.5	31	32.5
Length (in)	26	27	28	29	30	31	32	33

Packaging

Packaging	1 each per poly bag, 50 each per case							
Unit	Each							
Case Pack	50							
Case Weight (lb)	31.4	31.4	33.07	33.07	35.27	35.27	40	41.2
Case Dimensions (in)	19.69 x 12.2 x 18.9							