

**Style # 1245-OZ-RD**



**ironwear**<sup>®</sup>

ITEM#: 1245-OZ-RD  
 SIZE: MD  
 Class 2  
 Meets ANSI/ISEA 107-(year)  
 100% POLYESTER  
 Care Instructions:  
 Machine Wash warm, Tumble dry low, Do not bleach, Do not iron, Do not dry clean

Type R  
 Class 2  
 NOT FR

This garment is not flame resistant as defined by ANSI/ISEA 107-(year) Section 10.5

**RN95108  
 MADE IN CHINA**



(Front)



(Back)



(Side)

**Features**

- > **Description:** 100% polyester mesh safety vest with 2 radio clip holders and 2" reflective tape over contrasting fabric that extends over the shoulders, around the torso and in an H-pattern across the back
- > **Binding:** Hi-vis silver reflective and black polyester
- > **Material:** 100% polyester mesh fabric
- > **Color:** Hi-vis orange
- > **Standard:** ANSI/ISEA 107
- > **Class:** Type R, Class 2
- > **Closure:** Zipper front closure
- > **Tape:** 2" silver reflective tape over 3" hi-vis lime mesh fabric
- > **Pockets:** 11 Pockets - 2 waist pockets with flaps, 2 left chest pockets, 1 upper right chest pocket with 4 pen pockets overtop, 1 inside waist pocket and 1 inside tablet pocket

**Measurements**

Size	SM	MD	LG	XL	2XL	3XL	4XL	5XL
Width (in)	22	23.5	25	26.5	28	29.5	31	32.5
Length (in)	26	27	28	29	30	31	32	33

**Packaging**

Packaging	1 each per poly bag, 50 each per case							
Unit	Each							
Case Pack	50							
Case Weight (lb)	31.4	31.4	33.07	33.07	35.27	35.27	40	41.2
Case Dimensions (in)	19.69 x 12.2 x 18.9							