

Style #1256FR-LZ-RD



- > 100% flame-resistant cotton fabric safety vest, with 2 radio clip holders, high-visibility reflective tape over shoulders and around arms and torso



(Front)



(Back)

Features

- > **Material:** 100% flame-resistant cotton fabric
- > **Color:** Hi-vis lime
- > **Standard:** ANSI/ISEA 107, NFPA 2112, UL MH60361 registered and Arc Rating 8.7 ATPV, CAT2
- > **Class:** Type R, Class 3
- > **Closure:** Zipper front closure
- > **Tape:** 2" silver reflective tape
- > **Pockets:** 3 Pockets - 1 upper left chest pocket, 2 exterior waist pockets

WARNING
THIS GARMENT IS ONLY TO BE USED FOR FLASH FIRE PROTECTION. IF THIS GARMENT HAS COME IN CONTACT WITH FIRE, HAS BEEN WASHED MORE THAN 100 TIMES, OR THE WASHING INSTRUCTIONS HAVENOT BEEN FOLLOWED; PLEASE DISCARD THE GARMENT.

WASHING INSTRUCTIONS
MACHINE WASH AT 140°F AND TUMBLE DRY LOW AT 160°F. WHEN WASHING DO NOT USE CHLORINE BLEACH, STARCH, FABRIC SOFTENERS OR ANY PRODUCTS CONTAINING HYDROGEN PEROXIDE. FAILURE TO LAUNDRY PROPERLY COULD AFFECT THE FLAME RESISTANCE OF THE FABRIC.

100% COTTON
LOT NO. ---
MADE IN MEXICO
IRONWEAR
2020 SEABIRD WAY
RIVIERA BEACH, FL
ARC RATING 8.7 ATPV
CAT 2
DO NOT REMOVE

ironwear®
ITEM# 1256FR-LZ-RD
SIZE: XL
Class 3
Meets ANSI/ISEA 107-(year)
100% COTTON
Care Instructions:
Machine wash warm, Tumble dry low, Do not bleach, Do not iron, Do not dry clean

Type R
Class 3
FR: NFPA 2012-(year)
RN 95108
MADE IN MEXICO

ironwear®
ITEM#: 1256FR-LZ
SIZE: SM
CLASSIFIED
UL

FLAME RESISTANT CLOTHING FOR PROTECTION OF INDUSTRIAL PERSONNEL AGAINST SHORT DURATION THERMAL EXPOSURES FROM FIRE IN ACCORDANCE WITH NFPA 2112-(year) MH60361

THIS CLOTHING ITEM MEETS THE REQUIREMENTS OF NFPA 2112-(year) NFPA 2113 REQUIRES UPPER AND LOWER BODY COVERAGE
DO NOT REMOVE

Measurements

Size	SM	MD	LG	XL	2XL	3XL	4XL	5XL
Width (in)	24	24.5	26	27.5	29.5	31.5	33	36
Length (in)	29	28.5	28.5	28	30	30	30	30

Packaging

Packaging	1 each per poly bag, 25 each per case							
Unit	Each							
Case Pack	25							
Case Weight (lb)	26.6	28.7	30.8	32.8	35	37.1	39.2	41.3
Case Dimensions (in)	17.75 x 16.75 x 10	18 x 17.75 x 10.75	21.5 x 16 x 10			22 x 15 x 13.5		