


Style # 1287FR-LZ-RD



ironwear®

ITEM#: 1287FR-LZ-RD
 SIZE: MD
 Class 2
 Meets ANSI/ISEA 107
 100% POLYESTER
 Care Instructions:
 Machine Wash warm, Tumble dry low, Do not bleach, Do not iron, Do not dry clean

RN95108
 MADE IN CHINA

The fabric in this garment has been tested under ASTM test method D6413 and will Self-Extinguish when caught on fire. Self Extinguishing properties will diminish with washing

This garment should never be used when an arc flash or flash fire hazard is present. This garment is not flame resistant as defined by ANSI/ISEA 107 Section 10.5

Type R
 Class 2
 NOT FR



(Front)



(Back)

Description

- > **Features:** High visibility silver reflective tape in suspender pattern over top of shoulders as well as 360° continuous reflective, bands encircling the torso and 2 radio clip holders.
- > **Binding:** Lime Polyester
- > **Material:** 100% Polyester mesh fabric
- > **Color:** Lime
- > **Class:** Class 2
- > **Standard:** ANSI/ISEA 107
- > **Closure:** Zipper front closure
- > **Striping:** 2" silver reflecting tape on 4" hi-vis orange fabric
- > **Pockets:** 6 Pockets - 2 front lower flap pockets, 2 chest pockets, and 2 inside upper pockets.

> Flame Retardant Properties:

The treated fabric on this vest has been tested under test method D6413 and will Self-Extinguish when caught on fire. (After flame is less than 2.0 seconds average; Char length is less than 6" on average; and there is no melting or dripping). This vest should never be used where an Arc flash or Flash Fire is present.



Specifications

Size	S	M	L	XL	2XL	3XL	4XL	5XL
Width (cm/in)	55.9/22	59.7/23.5	63.5/25	67.3/26.5	71.1/28	74.9/29.5	78.7/31	82.6/32.5
Length (cm/in)	66/26	68.6/27	71.1/28	73.7/29	76.2/30	78.7/31	81.3/32	83.8/33

Packaging

Size	S	M	L	XL	2XL	3XL	4XL	5XL
Packaging	1 Per poly bag							
Unit	Each							
Case Pack	50							
Case Weight (lb/kg)	26.5/12		28.7/13		30.9/14			
Case Dimensions (in)	16.5" x 11" x 16.5"		16.5" x 11" x 17.3"		16.5" x 11" x 18.5"		16.5" x 11" x 19.3"	
Case Dimensions (cm)	42cm x 28cm x 42cm		42cm x 28cm x 44cm		42cm x 28cm x 47cm		42cm x 28cm x 49cm	