

Style # 1287-OZ-RD 6

ironwear

ITEM#: 1287-OZ-RD
 SIZE: MD
 Class 2
 Meets ANSI/ISEA 107
 100% POLYESTER
 Care Instructions:
 Machine Wash warm, Tumble
 dry low, Do not bleach, Do not
 iron, Do not dry clean

Type R
 Class 2
 NOT FR

This garment is not flame resistant as
 defined by ANSI/ISEA 107
 Section 10.5

RN95108
 MADE IN CHINA



(Front)



(Back)

Description

- > **Features:** High visibility silver reflective tape in suspender pattern over top of shoulders as well as 360° continuous reflective, bands encircling the torso and 2 radio clip holders.
- > **Binding:** Orange Polyester
- > **Material:** 100% Polyester mesh fabric
- > **Color:** Orange
- > **Class:** Class 2
- > **Standard:** ANSI/ISEA 107
- > **Closure:** Zipper front closure
- > **Striping:** 2" silver reflecting tape on 4" hi-vis lime fabric
- > **Pockets:** 6 Pockets - 2 front lower flap pockets, 2 chest pockets, and 2 inside upper pockets.

Specifications

Size	S	M	L	XL	2XL	3XL	4XL	5XL
Width (cm/in)	55.9/22	59.7/23.5	63.5/25	67.3/26.5	71.1/28	74.9/29.5	78.7/31	82.6/32.5
Length (cm/in)	66/26	68.6/27	71.1/28	73.7/29	76.2/30	78.7/31	81.3/32	83.8/33

Packaging

Size	S	M	L	XL	2XL	3XL	4XL	5XL
Packaging	1 Per poly bag							
Unit	Each							
Case Pack	50							
Case Weight (lb/kg)	26.5/12		28.7/13		30.9/14			
Case Dimensions (in)	16.5" x 11" x 16.5"		16.5" x 11" x 17.3"		16.5" x 11" x 18.5"		16.5" x 11" x 19.3"	
Case Dimensions (cm)	42cm x 28cm x 42cm		42cm x 28cm x 44cm		42cm x 28cm x 47cm		42cm x 28cm x 49cm	