

## Style # 1293BRK-L-RD



**ironwear**

ITEM#: 1293BRK-L-RD  
 SIZE: MD  
 Class 3  
 Meets ANSI/ISEA 107-(year)  
 100% POLYESTER  
 Care Instructions:  
 Machine Wash warm, Tumble dry low, Do not bleach, Do not iron, Do not dry clean

Type R  
 Class 3  
 NOT FR

This garment is not flame resistant as defined by ANSI/ISEA 107-(year) Section 10.5

RN95108  
 MADE IN CHINA



(Front)



(Back)

## Description

- > **Description:** Features high-visibility silver reflective tape in suspender pattern over top of shoulders as well as 360° continuous reflective and bands encircling the torso and radio clip equipped
- > **Binding:** Lime polyester
- > **Material:** 100% polyester mesh fabric
- > **Color:** Lime
- > **Standard:** ANSI/ISEA 107
- > **Class:** Type R, Class 3
- > **Closure:** 5 point breakaway on the two sides, two shoulders, and front closure
- > **Striping:** 2" silver tape on 4" orange fabric
- > **Pockets:** 6 pockets - 2 lower front flap pockets, 2 inside pockets, 2 upper chest pockets

## Specifications

Size	M	L	XL	2XL	3XL	4XL
Width (in/cm)	23.5 / 59.7	25 / 63.5	26.5 / 67.3	28 / 71.1	29.5 / 74.9	31 / 78.7
Length (in/cm)	27 / 68.6	28 / 71.1	29 / 73.7	30 / 76.2	31 / 78.7	32 / 81.3

## Packaging

Size	M	L	XL	2XL	3XL	4XL
Packaging	1 per poly bag					
Unit	Each					
Case Pack	50					
Case Weight (lb/kg)	33.5 / 15.2	36.4 / 16.5	38.6 / 17.5	40.8 / 18.5	43 / 33.5	
Case Dimensions (in)	19.7 x 12.2 x 18.5	19.7 x 12.2 x 19.3	19.7 x 12.2 x 20.1	19.7 x 12.2 x 20.9	19.7 x 12.2 x 21.7	
Case Dimensions (cm)	50 x 31 x 47	50 x 31 x 49	50 x 31 x 51	50 x 31 x 53	50 x 31 x 55	