

## Style #2160

- > Full body harness
- > ANSI Capacity: 130-310 lbs
- > OSHA Capacity: 420 lbs
- > ANSI Z359.11-2014
- > 3 ultra lightweight aluminum D-rings rated for at least 5,000 LBS/22 KN.
- > Five adjustments on chest, shoulders, and leg strap
- > Ultra lightweight aluminum grommet Adjustments on leg strap
- > Heavy duty tool belt
- > Back pad
- > Ultra lightweight aluminum quick release chest connector
- > Dual tool lanyard connection points for easy access
- > SRL independent web connector on back
- > Integrated sewn-in back support system
- > Ultra lightweight aluminum grommet adjustable belt
- > Shoulder pads
- > **Sizes:**  
SM  
SM-MD  
LG-XL  
2XL-3XL




(Front)



(Back)



(Back Pad/D-Ring/SRL Connector)



(Dual Tool Lanyard Connection Points)



(Integrated Sewn-In Back Support System)



(Ultra Lightweight Aluminum Quick Release Chest Connector)

## Packaging

- > **Color:** Blue / Black
- > **Unit:** Each
- > **Case Pack:** 4
- > **Case Weight:** 26.12lb / 11.85kg
- > **Case Dimensions:** 60cm x 40cm x 33cm
- > **Case Dimensions:** 23.5" x 15.75" x 13"