

Style #2420-SSH-LE

- > SRL (Self Retracting Lifeline)
- > Leading edge
- > 20ft Long steel cable
- > 360° Fully rotating steel snap hook
- > Gate strength 3,600lb
- > Tag line included
- > Carabiner included
- > Class B

Standards & Regulations

- > ANSI Z359.14-2014
- > OSHA 1926.502; 1910.66

Specifications

LE USE

- > **Capacity Range:** 130lb - 310lb
- > **Min. Setback Distance**
From Edge: 0'
- > **Min. Fall Clearance:** 17' - 21'
- > **Max Arrest Distance:** 54" - 102"
- > **Free Fall:** 5' Max

NON LE USE

- > **Capacity Range:** 130lb - 420lb
- > **Average Arresting Force:** 900lb
- > **Maximun Arresting Force:** 1,800lb
- > **Max Arrest Distance:** 54"
- > **Free Fall:** Not Permitted
- > **Min Fall Clearance:** 6.5'
- > **Class:** Class B SRL

Packaging

- > **Color:** Black
- > **Unit:** Each
- > **Case Pack:** 1
- > **Case Weight (lb/kg):** 14.02lb/6.36kg
- > **Case Dimensions (cm):** 29.3cm x 36.8cm x 12.7cm
- > **Case Dimensions (inch):** 11.53" x 14.5" x 5.0"

