Stock Code: 20415LEDDLP-ALB	Project Name:
Collection: Daphne	Location:
PRODUCT INFORMATION	Type:
Base: 20415 Parent: 20415LEDDLP Mounting Type: Wall UPC: 641594243253 Finish: N/A Diffuser: Alabaster	Quantity:Notes:
PRODUCT MEASUREMENTS	
FIXTURE Length: Width: 5.5" Diameter Height: 11.75" Extension: 4" Overall Height: BACKPLATE / CANOPY Length 8.5" Width: 4.25" Diameter: Height: 0.5"	
TECHNICAL SPECIFICATIONS	
SPECIFICATIONS Frame Material: Steel Diffuser Material: Glass Lamping Type: E-26 (Incandescent) Jbox: Standard Lamping Base: E-26 Lamp Wattage: 10 W Lamp Quantity: 1 Total Wattage: 10 W Voltage: 120v Lamps Included: No	
QUALIFICATIONS Location Rating Damp Certifitcation: UL (US/Canada) Listed ADA Compliant: Yes Energy Star: No JA8 Compliant: No Emergency Lighting: No Marine Grade: No Warranty: 1 Year	LINE DRAWING IES FILE 5.50°
PHOTOMETRICS Dimmable: Yes Nominial Lumens 800 Lm CRI: 90 Delivered Lumens: N/A CCT: 3000K Recommended Dimmers: (TRIAC)LEGRAND Titan CD703-PW; (ELV)LUTRON Skylark SELV-300P Additional Notes:	In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There

to the displayed and printed images. Signature:

Print Name Date:

