#### Stock Code: 20466LEDEM-CH/ACR Project Name: Location: Collection: Solero Type: PRODUCT INFORMATION Quantity: Base: 20466LEDEM Parent: 20466LEDEM Mounting Type: Ceiling UPC: 641594224740 Notes: Finish: Chrome Diffuser: Acrylic Lens PRODUCT MEASUREMENTS **FIXTURE BACKPLATE / CANOPY** Length: Length Width: Width: Diameter 18" Diameter: 18" Height: 4.75" Height: 1" Extension:

## **TECHNICAL SPECIFICATIONS**

### **SPECIFICATIONS**

Overall Height:

Frame Material: Steel Diffuser Material: Acrylic

Lamping Type: SSL (Dedicated LED) Jbox: Standard
Lamping Base: SSL Lamp Wattage: 30 W
Lamp Quantity: 1 Total Wattage: 30 W
Voltage: 120-277v Lamps Included: Yes

## **QUALIFICATIONS**

Location Rating Damp

Certifitcation: ETL (US/Canada) Listed

ADA Compliant: No Energy Star: No

JA8 Compliant: No Emergency Lighting: Yes

Marine Grade: No Warranty: 5 Year

# **PHOTOMETRICS**


Dimmable: No Nominial Lumens 2600 Lm CRI: 90 Delivered Lumens: 1510 Lm

CCT: 3000K

Recommended Dimmers:

#### Additional Notes:

Custom Finish 5 Piece Minimum Order Quantity; Optional Color Tempature 100 Piece Minimum Order Quantity



In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature:	
Print Name	Date:

