

Stock Code: **20831LEDDCS-WH/ACR**

Collection: ModPLUS

### PRODUCT INFORMATION

Base: 20831 Parent: 20831LEDDCS  
Mounting Type: Ceiling UPC: 641594239799  
Finish: White  
Diffuser: Acrylic Lens

### PRODUCT MEASUREMENTS

FIXTURE	BACKPLATE / CANOPY
Length:	Length:
Width:	Width:
Diameter 9"	Diameter:
Height: 0.5"	Height:
Extension:	
Overall Height:	

### TECHNICAL SPECIFICATIONS

#### SPECIFICATIONS

Frame Material: Acrylic  
Diffuser Material: Acrylic  
Lamping Type: SSL (Dedicated LED) Jbox: Pancake  
Lamping Base: SSL Lamp Wattage: 18 W  
Lamp Quantity: 1 Total Wattage: 18 W  
Voltage: 120v Lamps Included: Yes

#### QUALIFICATIONS

Location Rating: Damp  
Certification: ETL (US/Canada) Listed  
ADA Compliant: No Energy Star: No  
JA8 Compliant: Yes Emergency Lighting: No  
Marine Grade Finish: No  
Warranty: 5 Year

#### PHOTOMETRICS

Dimmable: Yes Nominal Lumens: 1400 Lm  
CRI: 90 Delivered Lumens: 1280 Lm  
CCT: Multi-CCTK  
Recommended Dimmers:  
(ELV)LUTRON Caseta PD - 6WCL; (ELV)LUTRON Maestro CL  
MACL-153M; (ELV)LUTRON Maestro MRF2-6CL;  
(TRIAC)LUTRON Diva DVCL-153P

#### ADDITIONAL NOTES

3 CCT Selectable Switch 3000K, 4000K, 5000K

Project Name: \_\_\_\_\_

Location: \_\_\_\_\_


Type: \_\_\_\_\_

Quantity: \_\_\_\_\_


Notes: \_\_\_\_\_



#### LINE DRAWING



#### IES FILE



In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: \_\_\_\_\_

Print Name: \_\_\_\_\_ Date: \_\_\_\_\_

Toll Free 800-828-5483 [www.AccessLighting.com](http://www.AccessLighting.com)

14410 Myford Road, Irvine, CA 92606

