

Stock Code: **20840LEDD-WH/ACR**

Collection: ModPLUS

### PRODUCT INFORMATION

Base: 20840 Parent: 20840LEDD  
Mounting Type: Ceiling UPC: 641594231335  
Finish: White  
Diffuser: Acrylic Lens

### PRODUCT MEASUREMENTS

FIXTURE	BACKPLATE / CANOPY
Length: 8.5"	Length
Width: 8.5"	Width:
Diameter	Diameter:
Height: 0.5"	Height:
Extension:	
Overall Height:	

### TECHNICAL SPECIFICATIONS

#### SPECIFICATIONS

Frame Material: Acrylic  
Diffuser Material: Acrylic  
Lamping Type: SSL (Dedicated LED) Jbox: Standard  
Lamping Base: SSL Lamp Wattage: 18 W  
Lamp Quantity: 1 Total Wattage: 18 W  
Voltage: 120-277v Lamps Included: Yes

#### QUALIFICATIONS

Location Rating Damp  
Certification: ETL (US/Canada) Listed  
ADA Compliant No Energy Star: No  
JA8 Compliant: No Emergency Lighting: No  
Marine Grade: No Warranty: 5 Year

#### PHOTOMETRICS


Dimmable: Yes Nominal Lumens 1800 Lm  
CRI: 80 Delivered Lumens: 1463 Lm  
CCT: 3000K  
Recommended Dimmers:  
(0-10V)LEVITON DD710-BLZ; (0-10V)LEVITON DS710-102; (0-10V)LUTRON NFTV-WH; (0-10V)LUTRON DVSTV-WH

Additional Notes:  
0-10V Source Dimming


Project Name: \_\_\_\_\_  
Location: \_\_\_\_\_  
Type: \_\_\_\_\_  
Quantity: \_\_\_\_\_  
Notes: \_\_\_\_\_



#### LINE DRAWING



#### IES FILE



In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: \_\_\_\_\_

Print Name \_\_\_\_\_ Date: \_\_\_\_\_

Toll Free 800-828-5483 [www.AccessLighting.com](http://www.AccessLighting.com)

14410 Myford Road, Irvine, CA 92606

The information is subject to change without notice. 9/23/2022 20840LEDD-WH\_ACR.pdf

