

Stock Code: **62559-MSS/STARRY**

Collection: Galaxy

**PRODUCT INFORMATION**

Base: 62559 Parent: 62559  
Mounting Type: Wall UPC: 641594223682  
Finish: Mirrored Stainless Steel  
Diffuser: Starry Night

**PRODUCT MEASUREMENTS**

<b>FIXTURE</b>	<b>BACKPLATE / CANOPY</b>
Length:	Length
Width: 24"	Width:
Diameter	Diameter:
Height: 4.75"	Height:
Extension: 6.25"	
Overall Height:	

**TECHNICAL SPECIFICATIONS**

**SPECIFICATIONS**

Frame Material: Stainless Steel	
Diffuser Material: Glass	
Lamping Type: G9 (Halogen)	Jbox: Standard
Lamping Base: G9	Lamp Wattage: 40 W
Lamp Quantity: 3	Total Wattage: 120 W
Voltage: 120v	Lamps Included: Yes

**QUALIFICATIONS**

Location Rating Damp	
Certification: UL (US/Canada) Listed	
ADA Compliant No	Energy Star: No
JA8 Compliant: No	Emergency Lighting: No
Marine Grade: No	Warranty: 1 Year

**PHOTOMETRICS**

Dimmable: Yes	Nominal Lumens 1440 Lm
CRI: 80	Delivered Lumens: N/A
CCT: 2900K	
Recommended Dimmers:	
(ELV)LUTRON Caseta PD - 6WCL; (ELV)LUTRON Skylark	
Contour CTCL-153P; (ELV)LUTRON Maestro CL MACL-153M;	
(TRIAC)LUTRON Diva DVCL-153P; (TRIAC)LEVITON Decora	
Sureslide 6674	

Additional Notes:

Project Name: \_\_\_\_\_

Location: \_\_\_\_\_


Type: \_\_\_\_\_

Quantity: \_\_\_\_\_

Notes: \_\_\_\_\_



**LINE DRAWING**



**IES FILE**

In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: \_\_\_\_\_

Print Name \_\_\_\_\_ Date: \_\_\_\_\_

**Toll Free 800-828-5483 www.AccessLighting.com**

14410 Myford Road, Irvine, CA 92606

