

Stock Code: **70003LED-BRZ**

Collection: Epiphanie

PRODUCT INFORMATION

Base: 70003 Parent: 70003LED
Mounting Type: Wall UPC: 641594101652
Finish: Bronze
Diffuser: N/A

PRODUCT MEASUREMENTS

FIXTURE	BACKPLATE / CANOPY
Length:	Length
Width: 5"	Width:
Diameter	Diameter: 5"
Height: 17"	Height: 1"
Extension: 1.75"	
Overall Height: 5-17"	

TECHNICAL SPECIFICATIONS

SPECIFICATIONS

Frame Material: Metal	
Diffuser Material: Glass	
Lamping Type: SSL (Dedicated LED)	Jbox: Standard
Lamping Base: SSL	Lamp Wattage: 3 W
Lamp Quantity: 1	Total Wattage: 3 W
Voltage: 120v	Lamps Included: Yes

QUALIFICATIONS

Location Rating Dry	
Certification: ETL (US/Canada) Listed	
ADA Compliant: No	Energy Star: No
JA8 Compliant: No	Emergency Lighting: No
Marine Grade: No	Warranty: 5 Year

PHOTOMETRICS

Dimmable: No	Nominal Lumens 165 Lm
CRI: 85	Delivered Lumens: N/A
CCT: 3500K	
Recommended Dimmers:	

Additional Notes:


Optional Pin-up parts (cord and plug) included; Custom Finish 100 Piece Minimum Order Quantity; Optional Color Temperature 100 Piece Minimum Order Quantity

Project Name: _____
 Location: _____
 Type: _____
 Quantity: _____
 Notes: _____



LINE DRAWING

IES FILE



In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: _____

Print Name _____ Date: _____

Toll Free 800-828-5483 www.AccessLighting.com

14410 Myford Road, Irvine, CA 92606

