

Stock Code: **R-63114-6/BS**

Collection: Rod

PRODUCT INFORMATION

Base: R-63114 Parent: R-63114-6
Mounting Type: N/A UPC: 641594225600
Finish: Brushed Steel
Diffuser: N/A

PRODUCT MEASUREMENTS

FIXTURE	BACKPLATE / CANOPY
Length: 6"	Length
Width:	Width:
Diameter	Diameter:
Height:	Height:
Extension:	
Overall Height:	

TECHNICAL SPECIFICATIONS

SPECIFICATIONS

Frame Material: N/A	
Diffuser Material: N/A	
Lamping Type: N/A	Jbox: N/A
Lamping Base: N/A	Lamp Wattage: N/A
Lamp Quantity: N/A	Total Wattage: N/A
Voltage: N/A	Lamps Included: No

QUALIFICATIONS


Location Rating Dry	
Certification: N/A	
ADA Compliant No	Energy Star: No
JA8 Compliant: No	Emergency Lighting: No
Marine Grade: No	Warranty: 1 Year

PHOTOMETRICS

Dimmable: No	Nominal Lumens N/A
CRI: N/A	Delivered Lumens: N/A
CCT: N/A	
Recommended Dimmers:	

Additional Notes:

Project Name: _____
Location: _____
Type: _____
Quantity: _____
Notes:



LINE DRAWING

IES FILE

In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: _____

Print Name _____ Date: _____

Toll Free 800-828-5483 www.AccessLighting.com

14410 Myford Road, Irvine, CA 92606

The information is subject to change without notice. 9/23/2022 R-63114-6_BS.pdf

