

Stock Code: **SA-FR-G9-4.5W-001DIM**

Collection: Bulb

### PRODUCT INFORMATION

Base: G9-LED Parent: SA-FR-G9-4.5W-  
Mounting Type: N/A UPC: 641594214048  
Finish: N/A  
Diffuser: N/A

### PRODUCT MEASUREMENTS

FIXTURE	BACKPLATE / CANOPY
Length:	Length
Width:	Width:
Diameter	Diameter:
Height:	Height:
Extension:	
Overall Height:	

### TECHNICAL SPECIFICATIONS

#### SPECIFICATIONS

Frame Material: N/A  
Diffuser Material: N/A  
Lamping Type: G9 (Replaceable LED) Jbox: N/A  
Lamping Base: G9 Lamp Wattage: 4.5 W  
Lamp Quantity: 1 Total Wattage: 4.5 W  
Voltage: 120v Lamps Included: Yes

#### QUALIFICATIONS

Location Rating Damp  
Certification: N/A  
ADA Compliant No Energy Star: No  
JA8 Compliant: No Emergency Lighting: No  
Marine Grade: No Warranty: 1 Year

#### PHOTOMETRICS

Dimmable: Yes Nominal Lumens 450 Lm  
CRI: 80 Delivered Lumens: N/A  
CCT: 3000K  
Recommended Dimmers:  
(ELV)LUTRON Skylark SELV-300P; (ELV)LUTRON Diva DVELV-303P; (ELV)LUTRON Diva DVELV-300P; (TRIAC)LUTRON Diva DV-600P

Additional Notes:

Project Name: \_\_\_\_\_

Location: \_\_\_\_\_

Type: \_\_\_\_\_

Quantity: \_\_\_\_\_

Notes:



LINE DRAWING

IES FILE

In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: \_\_\_\_\_

Print Name \_\_\_\_\_ Date: \_\_\_\_\_

Toll Free 800-828-5483 [www.AccessLighting.com](http://www.AccessLighting.com)

14410 Myford Road, Irvine, CA 92606

