

Stock Code: **TL-20147LEDDMGLP-BL**

Collection: Matira

PRODUCT INFORMATION

Base: TL-20147 Parent: TL-20147LEDDL
Mounting Type: Wall UPC: 641594242614
Finish: Black
Diffuser: N/A

PRODUCT MEASUREMENTS

FIXTURE	BACKPLATE / CANOPY
Length:	Length
Width: 4.75"	Width:
Diameter	Diameter:
Height: 7.75"	Height:
Extension: 6.5"	
Overall Height:	

TECHNICAL SPECIFICATIONS

SPECIFICATIONS

Frame Material: Steel
Diffuser Material: N/A
Lamping Type: E-26 (Incandescent) Jbox: N/A
Lamping Base: E-26 Lamp Wattage: 3 W
Lamp Quantity: 1 Total Wattage: 3 W
Voltage: 120v Lamps Included: Yes

QUALIFICATIONS

Location Rating Wet
Certification: UL (US/Canada) Listed
ADA Compliant: No Energy Star: No
JA8 Compliant: No Emergency Lighting: No
Marine Grade Finish: Yes
Warranty: 5 Year

PHOTOMETRICS

Dimmable: No Nominal Lumens 70 Lm
CRI: N/A Delivered Lumens: N/A
CCT: Amber598nmK
Recommended Dimmers:


ADDITIONAL NOTES

Custom Finish 5 Piece Minimum Order Quantity

Project Name: _____
Location: _____
Type: _____
Quantity: _____
Notes: _____



LINE DRAWING



IES FILE

In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: _____

Print Name _____ Date: _____

Toll Free 800-828-5483 www.AccessLighting.com

14410 Myford Road, Irvine, CA 92606

The information is subject to change without notice. 12/22/2022 TL-20147LEDDMGLP-BL.pdf

