

Stock Code: **TP-GU10G6LED5.3W120V**

Collection: Bulb

### PRODUCT INFORMATION

Base: GU10-LED Parent: TP-GU10G6LED  
Mounting Type: N/A UPC: 641594222722  
Finish: N/A  
Diffuser: N/A

### PRODUCT MEASUREMENTS

FIXTURE	BACKPLATE / CANOPY
Length:	Length
Width:	Width:
Diameter	Diameter:
Height:	Height:
Extension:	
Overall Height:	

### TECHNICAL SPECIFICATIONS

#### SPECIFICATIONS

Frame Material: Glass  
Diffuser Material: N/A  
Lamping Type: GU-10 (Replaceable LE Jbox: N/A)  
Lamping Base: GU-10 Lamp Wattage: 5.5 W  
Lamp Quantity: 1 Total Wattage: 5.5 W  
Voltage: 120v Lamps Included: Yes

#### QUALIFICATIONS

Location Rating Damp  
Certification: UL (US/Canada) Listed  
ADA Compliant No Energy Star: No  
JA8 Compliant: No Emergency Lighting: No  
Marine Grade: No Warranty: 1 Year

#### PHOTOMETRICS

Dimmable: Yes Nominal Lumens 380 Lm  
CRI: 80 Delivered Lumens: 380 Lm  
CCT: 3000K  
Recommended Dimmers:  
(TRIAC)LEGRAND Titan CD703-PW; (ELV)LUTRON Skylark  
SELV-300P; (MLV)COOPER Aspire 9530SW

Additional Notes:

Project Name: \_\_\_\_\_

Location: \_\_\_\_\_

Type: \_\_\_\_\_

Quantity: \_\_\_\_\_

Notes:



LINE DRAWING

IES FILE

In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: \_\_\_\_\_

Print Name \_\_\_\_\_ Date: \_\_\_\_\_

Toll Free 800-828-5483 [www.AccessLighting.com](http://www.AccessLighting.com)

14410 Myford Road, Irvine, CA 92606

The information is subject to change without notice. 9/23/2022 TP-GU10G6LED5.3W120V.pdf

