



C30ELBK



41.5" x 30" x 23.63" (H x W x D)

30 inch wide all-in-one kitchenette in black with a 2-burner 115V coil cooktop, 2-door refrigerator-freezer, sink, and storage cabinet

Highlights:

Complete all-in-one convenience with a refrigerator-freezer, cooktop, sink, and storage compartment in just 30"

Black and stainless steel exterior finish brings a modern look to your kitchen space

ENERGY STAR certified 2-door refrigerator-freezer included

Product Features:

Complete one-piece kitchenette	All-in-one kitchen is built with virtually everything you need for meal preparation
Refrigerator-freezer included	CP34BSS is packaged inside the kitchenette. This 3.2 cu.ft. ENERGY STAR certified refrigerator includes adjustable glass shelves, door storage, and a freezer compartment
Sink and faucet	Stainless steel sink with ready-to-use faucet included
2-burner cooktop	Includes two coil elements, with a rear 500W burner and front 900W burner to accommodate a range of heating options
115V operation with pre-installed cords	Both the cooktop (12 amps) and refrigerator (1.1 amps) include 3-pronged cords for easy setup
Push-to-turn knobs	Cooktop knobs require a small amount of force to turn the elements on, helping to prevent accidents
Indicator lights	Operating indicators light up to show which burner is in use
Black and stainless steel exterior finish	Modern design with a jet black powder-coated metal cabinet, stainless steel surface, and stainless steel refrigerator doors
One piece stainless steel countertop	Easy-to-clean surface with a professional look



C30ELBK Specifications:

Overview	
Height of Cabinet	41.5" (105 cm)
Width	30.0" (76 cm)
Depth	23.63" (60 cm)
Depth with Handle	24.63" (63 cm)
Depth with door at 90°	41.88" (106 cm)
Capacity	3.2 cu.ft. (91 L)
Defrost Type	Cycle
Door	Black/SS
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	13.1
Voltage/Frequency	115 V AC/60 Hz
Weight	108.0 lbs. (49 kg)
Shipping Weight	113.0 lbs. (51 kg)
Estimated Time to Ship	Next day shipping
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Kitchenette	
Refrigerator Included	CP34BSS
Refrigerator Door Swing	RHD
Reversible	Yes
Adjustable Shelves	Yes
Shelf Type	Glass
Shelf Qty	2
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Full Door Shelves	2
Can Storage	Yes
Thermostat Type	Dial
Interior Light	Yes
Refrigerant Type	R600a
Refrigerant Amount	1.16 oz.
High Side PSI	250.0
Low Side PSI	88.0
Cooking Type	Coil Cooktop

Number of Burners	2
Cooktop Controls	Dial
Interior Height 1	18.5" (47 cm)
Interior Width 1	15.75" (40 cm)
Interior Depth 1	15.0" (38 cm)
Interior Height 2	7.5" (19 cm)
Interior Width 2	14.0" (36 cm)
Interior Depth 2	14.0" (36 cm)

