



# CK36EL



40" x 36.13" x 23.63" (H x W x D)

36 inch wide all-in-one kitchenette in black with a 2-burner 115V radiant cooktop, 2-door refrigerator-freezer, sink, and storage cabinet

### Highlights:

Complete all-in-one convenience with a refrigerator-freezer, cooktop, sink, and storage compartment in just 36"

Black and stainless steel exterior finish brings a modern look to your kitchen space

ENERGY STAR certified 2-door refrigerator-freezer included

### Product Features:

Complete one-piece kitchenette	All-in-one kitchen is built with virtually everything you need for meal preparation
2-door refrigerator-freezer included	CP34BSS is packaged inside the kitchenette. This 3.2 cu.ft. ENERGY STAR certified refrigerator includes adjustable glass shelves, door storage, and a freezer compartment
Sink and faucet	Stainless steel sink with ready-to-use faucet included
2-burner cooktop	Includes two coil elements, with a rear 500W burner and front 900W burner to accommodate a range of heating options
115V operation with pre-installed cords	Both the cooktop (12 amps) and refrigerator (1.1 amps) include 3-pronged cords for easy setup
Push-to-turn knobs	Cooktop knobs require a small amount of force to turn the elements on, helping to prevent accidents
Indicator lights	Operating indicators light up to show which burner is in use
Black and stainless steel exterior finish	Modern design with a jet black powder-coated metal cabinet, stainless steel surface, and stainless steel refrigerator doors
One piece stainless steel countertop	Easy-to-clean surface with a professional look



## CK36EL Specifications:

Overview	
Height of Cabinet	40.0" (102 cm)
Width	36.13" (92 cm)
Depth	23.63" (60 cm)
Depth with Handle	24.63" (63 cm)
Depth with door at 90°	41.88" (106 cm)
Capacity	3.2 cu.ft. (91 L)
Defrost Type	Cycle
Door	Black/SS
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	13.1
Voltage/Frequency	115 V AC/60 Hz
Weight	111.0 lbs. (50 kg)
Shipping Weight	116.0 lbs. (53 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Kitchenette	
Refrigerator Included	CP34BSS
Refrigerator Door Swing	RHD
Reversible	Yes
Adjustable Shelves	Yes
Shelf Type	Glass
Shelf Qty	1
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Full Door Shelves	2
Can Storage	Yes
Thermostat Type	Dial
Interior Light	Yes
Refrigerant Type	R600a
Refrigerant Amount	1.16 oz.
High Side PSI	250.0
Low Side PSI	88.0
Cooking Type	Coil Cooktop
Number of Burners	2

Cooktop Controls		Dial
Interior Height 1		18.5" (47 cm)
Interior Width 1		15.75" (40 cm)
Interior Depth 1		15.0" (38 cm)
Interior Height 2		7.5" (19 cm)
Interior Width 2		14.0" (36 cm)
Interior Depth 2		14.0" (36 cm)
Sink Height		7.25" (18 cm)
Sink Width		12.0" (30 cm)
Sink Depth		12.0" (30 cm)

