



CR2B12ST



3" x 11.75" x 19.75" (H x W x D)

115V 2-burner radiant cooktop with smooth black ceramic glass surface, stainless steel trim, and pre-installed cord

Highlights:

Smooth black EuroKera ceramic glass surface offers easy cleanup and modern style

Two-burner electric cooktop with 115V operation

Residual heat indicator for added safety

Product Features:

Black ceramic glass surface	Smooth EuroKera surface offers modern style in an easy-to-clean design
Two heating elements	One 900W and one 500W burner to meet a variety of cooking needs
Stainless steel trim	Provides added elegance to your kitchen
Indicator lights	Show when and which burners are turned on
Residual heat indicator light	Offers added safety by alerting when burners are too hot to touch
Push-to-turn controls	Prevents accidents by requiring a small amount of force to turn on cooktop heat
115V operation	Standard 3-pronged 115V cord included for use with 20 amp circuits
Cord included	Ships with standard 3-pronged cord pre-installed
ADA compliant design	Upfront, easy-to-turn controls help to comply with ADA guidelines for accessibility



CR2B12ST Specifications:

Overview	
Height of Cabinet	3.0" (8 cm)
Width	11.75" (30 cm)
Depth	19.75" (50 cm)
Cabinet	Black Glass
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	20.0
Voltage/Frequency	115 V AC/60 Hz
Weight	12.0 lbs. (5 kg)
Shipping Weight	17.0 lbs. (8 kg)
Parts & Labor Warranty	1 Year
UPC	761101063096
Electric Cooktop	
Heating Type	Radiant
Surface	Glass
Element Type	Glasstop
Number of Elements	2
controls	Dial
Countertop Cutout Width	11.0" (28 cm)
Countertop Cutout Depth	19.0" (48 cm)
Element #1 Size	5.5" (14 cm)
Element #1 Wattage	500.0
Element #2 Size	7.0" (18 cm)
Element #2 Wattage	900.0
Cutout Height	5.0" (13 cm)
Cutout Width	11.0" (28 cm)
Cutout Depth	19.0" (48 cm)

