



GCJ536SS



2.88" x 33.88" x 20" (H x W x D)

5-burner gas cooktop made in Italy with sealed burners, multiple heating outputs, a 304 grade stainless steel surface, and continuous cast iron grates

Highlights:

5 sealed burners provide optimal heating options in a modern design

304 grade stainless steel surface ensures durability and elegance

Continuous cast iron grates offer easy use of the multiple burners

Product Features:

304 grade stainless steel surface	Long-lasting durability in a sleek design
Sealed burners	Quality burners by Defendi with cast iron caps ensure lasting durability and easier cleanup
34" wide surface	Allows for easy use of multiple cooking vessels without hitting or banging
Smooth edge design	Provides added safety and blends cleanly into countertops
Push-to-turn knobs	Safety feature requires you to turn the knob to the "full-on" position before pushing down, waiting for the ignition, and adjusting to your preferred heating level
Designer knobs	Heavy duty brass and aluminum knobs in a round design and steel finish for a modern look
Conversion kit included	Convert operation from natural gas to LP with the included kit
Continuous cast iron grates in a matte finish	Solid cast iron construction to support heavy cookware, with a continuous design that makes it easy to move pots to a different burner
Wok ring included	Removable ring included to safely hold a wok over the flame when cooking on the left-side burner



GCJ536SS Specifications:

Overview

Height of Cabinet	2.88" (7 cm)
Width	33.88" (86 cm)
Depth	20.0" (51 cm)
Cabinet	Stainless Steel
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	1.0
Voltage/Frequency	115 V AC/60 Hz
Weight	34.0 lbs. (15 kg)
Shipping Weight	39.0 lbs. (18 kg)
Parts & Labor Warranty	1 Year
UPC	761101064314

Gas Cooktop

Ignition	Electric
LP Convertible	Yes
Number of Burners	5
Controls	Dial
Surface	Stainless Steel
Grate Material	Cast iron
Cutout Width	32.75" (83 cm)
Cutout Depth	18.75" (48 cm)
Burner #1 BTU	15300.0
Burner #2 BTU	6000.0
Burner #3 BTU	3400.0
Burner #4 BTU	10000.0
Burner #5 BTU	6000.0

