



# MB13G



20.25" x 15.88" x 16.75" (H x W x D)

Compact minibar designed for the display and refrigeration of beverages and sealed food, with a reversible glass door, front lock, and black cabinet

### Highlights:

Compact size is ideal for use in hotels and suites

Quiet compressor-based cooling system keeps stored items cold

Glass door provides a full display of stored items

### Product Features:

Compact dimensions	Slim fit offers the ideal choice for hotel rooms and other settings with limited counter and cabinet space
Double pane tempered glass door	Ideal for displaying stored contents to your guests
Commercial design	Meets UL-471 commercial standards
Digital controls	Easy temperature management with a digital control panel that lets you choose between six temperature levels at the touch of a button
Compressor-based cooling system	Quiet operation with a true refrigeration system that keeps stored items cold
Quiet operation	Runs at just 33.5 dB for a quiet performance that won't disturb your guests
Factory installed lock	Front lock offers convenient security, with two keys included
Reversible door	User-reversible door swing for added flexibility
Adjustable shelving	Attractive plastic shelf included, with seven glide positions to allow you to accommodate a range of sizes



## MB13G Specifications:

Overview	
Height of Cabinet	20.25" (51 cm)
Width	15.88" (40 cm)
Depth	16.75" (43 cm)
Depth with door at 90°	31.5" (80 cm)
Capacity	0.9 cu.ft. (25 L)
Defrost Type	Automatic
Door	Glass
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Energy Usage/Year	259.0kWh/year
Amps	0.4
Voltage/Frequency	115 V AC/60 Hz
Weight	36.0 lbs. (16 kg)
Shipping Weight	40.0 lbs. (18 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101065304
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Plastic
Shelf Qty	1
Adjustable Shelves	Yes
Thermostat Type	Digital
Fan Type	Interior
Refrigerant Type	R600a
Refrigerant Amount	0.85oz.
High Side PSI	106.0
Low Side PSI	55.0
Interior Light	Yes
Temperature Range	34 - 46 °F
Sound Level	33.5 dB
Dimensions	
Interior Height	15.88" (40 cm)
Interior Width	12.25" (31 cm)
Interior Depth	8.5" (22 cm)
Compressor Step Height	7.5" (19 cm)

Compressor Step Width	12.25" (31 cm)
Compressor Step Depth	1.5" (4 cm)

