

# New Product Introduction

# Capture

## Full HD, frameless video surveillance monitors



EXCLUSIVE  
@ADI

### Applications:

These full HD, frameless LED monitors are designed to excel in 24/7 video surveillance applications. 16.7 million colors display every detail, while HDMI and VGA inputs, source auto detection and quick touch scalability help to ensure easy installation.

### Features:

- Sleek frameless design
- 24/7 operation
- 1920x1080 full HD resolution
- Low blue light
- Source auto detection and quick touch scalability
- UL/cUL certified

## Video Surveillance Monitors:

| Part Number              | Viewing Size | Resolution            | Description   |
|--------------------------|--------------|-----------------------|---|
| 0E-24VGDHDMI2 <b>NEW</b> | 23.8"        | 1920x1080             | <b>Frameless LED Monitors:</b> VGA and HDMI inputs, source auto detection, quick touch scalability, 24/7 operation, UL listed   |
| 0E-27VGDHDMI2 <b>NEW</b> | 27"          |                       |   |
| 0E-19VGHDMI2             | 18.5"        | 1366x768              | <b>LED Monitors:</b> VGA and HDMI inputs, source auto detection, quick touch scalability, 24/7 operation, UL listed   |
| 0E-22VGHDMI2             | 21.5"        | 1920x1080             |   |
| 0E-24EVGHDMI             | 23.8"        | 1920x1080             | <b>Energy Efficient LED Monitors:</b> ECO mode motion detection, VGA and HDMI inputs, IPS technology, source auto detection, quick touch scalability, 24/7 operation, UL listed |
| 0E-27EVGHDMI             | 27"          |                       |   |
| 0E-20LED2                | 19.53"       | 1920x1080             | <b>BNC Looping LED Monitors:</b> VGA, BNC and HDMI inputs, IPS technology, source auto detection, quick touch scalability, 24/7 operation, UL listed                            |
| 0E-22LED2                | 21.5"        |                       |   |
| 0E-24LED2                | 23.6"        |                       |   |
| 0E-27LED2                | 27"          |                       |   |
| 0E-32LEDMON2             | 31.5"        |                       |   |
| 0E-28LED4K2              | 28"          | 3860x2160             | <b>4K Ultra HD LED Monitor:</b> DVI, VGA, BNC, HDMI, USB, Audio and RJ45 inputs, source auto detection, quick touch scalability, 24/7 operation, UL listed                      |
| 0E-32MON720P             | 32"          | 1366x768<br>400 nits  | <b>High Brightness LED Monitors:</b> VGA, HDMI, USB and AV inputs, source auto detection, quick touch scalability, 16/7 operation, UL listed                                    |
| 0E-43MON1080             | 43"          | 1920x1080<br>500 nits |   |