

FULL HD PRO-GRADE LED COLOR MONITOR

24/7/365 Operating Capability



This professional-grade widescreen LED 23.6" color monitor offers HDMI, VGA and BNC inputs. With the BNC looping output, its versatility will allow it to work for any application. Boasting 16.7 million colors and FHD resolution, this monitor will make your video come to life.

FEATURES

- 23.6" Diagonal Viewing Size
- 1920x1080P Full HD Resolution
- VGA, BNC and HDMI Inputs
- IPS Technology, 178° Viewing Angle
- Source Auto Detection
- Quick Touch Scalability 16:9/4:3
- Includes Audio, VGA, HDMI and Power Cables
- 30-Month Warranty
- Part #: OE-24LED2
- UPC: 811914029779
- Length: 21.88"
- Width: 5.87"
- Height: 15.69"
- Weight: 9.0 lbs.
- UL Listing



MONITEUR COULEUR HD INTÉGRALE À DEL DE QUALITÉ PROFESSIONNELLE

Capacité de fonctionnement 24/7/365



Ce moniteur couleur de 23,6 po à DEL de qualité professionnelle est doté d'entrées HDMI, VGA et BNC. Grâce à sa sortie BNC à bouclage supplémentaire qui lui procure une polyvalence accrue, ce moniteur fonctionnera pour de nombreuses applications. Avec ses 16,7 millions de couleurs et sa résolution FHD, ce moniteur vous permettra de visionner des vidéos de qualité inégalée.

CARACTÉRISTIQUES

- Dimensions d'affichage diagonales de 23,6 po
- Résolution Full HD 1920x1080 p
- Entrées VGA, BNC et HDMI
- Technologie IPS - angle de vue de 178°
- Détection automatique de la source
- Mise à l'échelle Quick Touch 16:9/4:3
- Comprend des câbles audio, VGA, HDMI et d'alimentation
- Garantie de 30 mois
- N° de pièce : OE-24LED2
- UPC : 811914029779
- Longueur : 21,88 po
- Largeur : 5,87 po
- Hauteur : 15,69 po
- Poids : 9,0 lb
- Homologué UL



Model	OE-24LED2
Screen Diagonal Dimension (inches)	23.6"
Viewable Area W x H (inches)	20.52" x 11.54"
LED Type	Edge LED
Pixel Pitch (mm)	0.2715mm x 0.2715mm
Screen Maximum Resolution	1920x1080
Display Resolutions	640x480; 800x600; 1024x768; 1280x1024; 1600x900; 1920x1080
Supported Input Resolutions	640x480; 800x600; 1024x768; 1280x1024; 1600x900; 1920x1080
Refresh Rate (hertz)	60Hz
Color Depth (millions)	16.7 million colors
Brightness (cd/m ²)	250 cd/m ²
Auto Adjust	Yes
Monitor Aspect Ratio	16:9
Display Aspect Ratio	OSD selectable 16:9 or 4:3
Horizontal TV Lines	1080
Contrast Ratio	1000:1SCR
Response Time (ms)	5 ms (GTG)
View Angle H/V (degrees)	178° x 178°/CR>10
Digital Video Inputs	HDMI up to 1920x1080
Analog Video In/Out	VGA up to 1920x1080, BNC CVBS looping
Audio Inputs (stereo)	1 x 3.5mm mini-jack
Speakers (watts)	2 x 3 watts
Stand-by (watts)	<0.5 watt
Power Consumption (watts)	25 watts typical
Monitor Body Dimensions (inches)	21.88" x 2" x 13.28"
Dimensions Monitor+Stand (inches)	21.88" x 5.87" x 15.69"
Panel Surface	Matte black
Case and Stand Material	Plastic
VESA Mounting Pattern (mm)	100mm x 100mm
Base/Stand Included	Yes
Base Tilt Angle	-5°-15°
Weight Cabinet Only (lbs.)	8.5 lbs.
Weight Cabinet+Base Stand (lbs.)	9.0 lbs.
Power Supply (internal)	AC 100-240V-50/60Hz 1.1A
Operating Temperature	0°C-40°C / 32°F-104°F
Storage Temperature	-20°C-50°C / -4°F-122°F
Operating Humidity	10-90%
Accessories Included in the Box	Power cable/HDMI cable/VGA cable/Audio cable/IR Remote/Batteries Hinge cover/Screws/Base of stand/Stand support/User manuals
Rack Mount Screw Size (mm)	Screws for Mounting Monitor, Screws Type: BMØ4.0x6mm/4pcs/ BMØ4.0x8mm/4pcs Screws for Securing Base of Stand, Screws Type: BBØ4.0x7mm/5pcs Screws for Installing Monitor Stand, Screws Type: BMØ4.0x8mm/2pcs
Certifications	CE/FCC/RoHS/HDMI/UL/WEEE/REACH
Warranty	30 Months

FOR MORE INFORMATION, CONTACT YOUR ADI SALES PERSON.