

# FIBERGLASS ROD KIT

## 30' LENGTH, WITH ACCESSORIES

**ADI**  
**PRO**

This ADI PRO fiberglass glow rod kit extends to 30 feet and is used to push and pull wire and cable in low-light environments. Flexible, strong glow rods are splinter-free and include durable brass connectors and ends. The kit also features multiple accessories for maximum versatility.



## FEATURES

Translucent green fiberglass for high visibility

Durable brass connectors allow for easy extension of rods or disassembly for transportation

Pull strength:

- Fiberglass rods tested up to 500 lbs. (227kg)
- Assembly with connectors tested up to 176 lbs. (80kg)

Standard 3/16" outside diameter (OD)

Includes five 6' rods: one with a bullnose male connector for maximum strength and four with male to female connectors

Accessories include: lighted bullnose male connector, bullnose to female threaded connector, 12" ball chain connector, whisk tip

Limited Lifetime Warranty

## Product Specifications

PART # 0E-30RODKIT

Dimensions: 30' L x 3/16" OD



For more information contact your ADI Sales person or visit [adiglobal.com/adiexclusivebrands](http://adiglobal.com/adiexclusivebrands)

# TROUSSE DE TIGES EN FIBRE OPTIQUE

## 30 PI, AVEC ACCESSOIRES

**ADI**  
**PRO**

Cette trousse de tiges lumineuses, pouvant atteindre 30 pi, sert à pousser ou à tirer des fils et des câbles dans des environnements à faible éclairage. Les tiges, flexibles et robustes, sont sans saillies et présentent des connecteurs et des embouts en laiton durables. La trousse contient également des accessoires pour plus de polyvalence.



## CARACTÉRISTIQUES

En fibre de verre verte transparente pour une haute visibilité

Connecteurs en laiton durables pour une extension facile des tiges ou pour le désassemblage lors du transport

Résistant à une tension (lb/kg):

- Jusqu'à 500 lb (227kg) pour les tiges en fibre optique
- Jusqu'à 176 lb (80kg) pour montage avec connecteurs

Diamètre extérieur standard (3/16 po)

Comprend cinq tiges de 6 pi: une avec un connecteur arrondi mâle pour un maximum de force et quatre avec des connecteurs mâle-femelle

Accessoires: connecteur mâle arrondi éclairé, connecteur filé arrondi-femelle, connecteur de chaîne 12 po, connecteur whisk

Garantie à vie limitée

## Caractéristiques techniques

NO DE PIÈCE: 0E-30RODKIT

Dimensions: 30 pi (longueur) x 3/16 po (diamètre extérieur)



Pour de plus amples renseignements, communiquez avec un représentant ADI ou visitez la page [fr.adiglobaldistribution.ca](http://fr.adiglobaldistribution.ca)