

FIBERGLASS RODS

6' LENGTH

ADI
PRO

ADI PRO's 6-foot fiberglass glow rods are used to push and pull wire and cable in low-light environments. These flexible, strong glow rods are splinter-free and include durable brass connectors and ends. Three models are available, featuring male to female or bullnose to female connectors, or pulling eye ends.



FEATURES

Translucent green fiberglass for high visibility

Durable brass connectors allow for easy extension of rods or disassembly for transportation

Pull strength:

- Fiberglass rods tested up to 500 lbs. (227kg)
- Assembly with connectors tested up to 176 lbs. (80kg)

Standard 3/16" outside diameter (OD)

Model with bullnose connector provides extra strength

Limited Lifetime Warranty

Product Specifications

PART #

0E-6ROD*

0E-6RODBNFM*

0E-6RODMF*



Pulling
Eye

Bullnose to
Female

Male to
Female

*Individual glow rods not available in Canada. See kits.

Dimensions: 6' L x 3/16" OD



For more information contact
your ADI Sales person or visit
adiglobal.com/adiexclusivebrands