

# FIBERGLASS RODS

## 6' LENGTH



ADI PRO's 6-foot fiberglass glow rods are used to push and pull wire and cable in low-light environments. These flexible, strong glow rods are splinter-free and include durable brass connectors and ends. Three models are available, featuring male to female or bullnose to female connectors, or pulling eye ends.



## FEATURES

Translucent green fiberglass for high visibility

Durable brass connectors allow for easy extension of rods or disassembly for transportation

Pull strength:

- Fiberglass rods tested up to 500 lbs. (227kg)
- Assembly with connectors tested up to 176 lbs. (80kg)

Standard 3/16" outside diameter (OD)

Model with bullnose connector provides extra strength

Limited Lifetime Warranty

## Product Specifications

### PART #

0E-6ROD\*

0E-6RODBNFM\*

0E-6RODMF\*



Pulling  
Eye

Bullnose to  
Female

Male to  
Female

\*Individual glow rods not available in Canada. See kits.

Dimensions: 6' L x 3/16" OD



For more information contact your ADI Sales person or visit [adiglobal.com/adiexclusivebrands](http://adiglobal.com/adiexclusivebrands)