

PROXIMITY CREDENTIALS

PRE-PROGRAMMED, 34 BIT/N10002



These proximity credentials are pre-programmed with 34 bit/N10002 formatting and are available as clamshell or ISO cards. Our 34 bit credentials deliver contactless access control with exceptional durability and value.



FEATURES

Compatible with 125kHz proximity readers programmed for 34 bit/N10002 format

Durable ABS or PVC construction with passive design (no battery) for long-term use

Conveniently pre-programmed (34 bit/N10002 format)

Always in stock

4-Year Warranty

Product Specifications

Frequency: 125kHz

Format: 34 bit/N10002

Quantity: 25-pack

PRODUCT #	Features	Dimensions	Weight	Materials	Operating Temp.
0E-CLAM34P25 Clamshell	Vertical slot	3.37" x 2.125" x 0.075" (8.56 x 5.4 x 0.19cm)	0.317 oz. (9g)	ABS shell PVC label	-50° to 160°F (-45° to 70°C)
0E-ISO34P25 ISO	Printable No slot	3.37" x 2.125" x 0.033" (8.56 x 5.4 x 0.084cm)	0.212 oz. (6g)	PVC	-50° to 160°F (-45° to 70°C)

For more information contact your ADI Sales person or visit adiglobal.com/adiexclusivebrands