



12 FT HIGH SPEED HDMI® CABLE WITH ETHERNET

0E-HDMI12

SPECIFICATIONS:

- Supports UHD 4K & 2K @60Hz and 1080p
- HDMI ethernet channel
- Data speed transfer: exceeds 10.2 gbps
- Audio return channel
- Allows 3D over HDMI when connected to 3D devices
- Additional color spaces (sYCC601, RGB & YCC601)
- Triple shielded cable with copper connectors
- Limited Lifetime Warranty
- UL Listed - CL3 Rated

PART#: 0E-HDMI12
UPC: 811914021568
LENGTH: 12 FT
WEIGHT: .52 LBS

CABLE CONSTRUCTION	28 AWG
JACKET OUTER	7.3 MM
DIMENSION	
MINIMUM BEND RADIUS	60 MM
MAXIMUM COLOR DEPTH	48-BIT, 16 BITS PER COLOR
MAXIMUM REFRESH RATE	1080P 120HZ SOURCE CONTENT
HDMI HIGH SPEED	YES
ETHERNET	YES
AUDIO RETURN CHANNEL	YES
DEEP COLOR SUPPORT	YES
3D COMPATIBLE	YES
4K SUPPORT	YES
AUDIO SUPPORT	DTS, DOLBY DIGITAL

For more information please call 1-833-574-9124
 or email AVARRO@adiglobal.com

To learn more about AVARRO products visit
avarro.adiglobaldistribution.us

