



25 FT HIGH SPEED HDMI® CABLE WITH ETHERNET

0E-HDMIP25



SPECIFICATIONS:

- Full 18GBPS bandwidth
- UltraHD, 4K@60Hz, 4:4:4 Chroma Sampling
- Enables transmission of High Dynamic Range (HDR) video
- EMI tested to ensure cables minimize interference with wireless signals
- 100% aluminum shielded connector, 360 degrees of coverage
- UL Listed - CL3 Rated
- Limited Lifetime Warranty

PART#: 0E-HDMIP25
UPC: 811914027553
LENGTH: 25 FT
WEIGHT: 1.5 LBS

CABLE CONSTRUCTION	24 AWG
JACKET OUTER DIMENSION	9.0 MM
MINIMUM BEND RADIUS	60 MM
MAXIMUM COLOR DEPTH	48-BIT, 16 BITS PER COLOR
MAXIMUM REFRESH RATE	4K 60 HZ + HDR
HDMI HIGH SPEED	YES
ETHERNET	YES
AUDIO RETURN CHANNEL	YES
DEEP COLOR SUPPORT	YES
3D COMPATIBLE	YES
4K SUPPORT	YES
AUDIO SUPPORT	DTS-HD DOLBY TRUEHD, ATMOS

For more information please call 1-833-574-9124 or email AVARRO@adiglobal.com

To learn more about AVARRO products visit avarro.adiglobaldistribution.us

