



# 35 FT HIGH SPEED HDMI® CABLE WITH ETHERNET

0E-HDMIP35

## SPECIFICATIONS:

- Full 18GBPS bandwidth
- UltraHD, 4K@60Hz, 4:4:4 Chroma Sampling
- Enables transmission of High Dynamic Range (HDR) video
- EMI tested to ensure cables minimize interference with wireless signals
- 100% aluminum shielded connector, 360 degrees of coverage
- UL Listed - CL3 Rated
- Limited Lifetime Warranty

**PART#:** 0E-HDMIP35  
**UPC:** 840049302167  
**LENGTH:** 35 FT  
**WEIGHT:** 2.6 LBS

CABLE CONSTRUCTION	24 AWG
JACKET OUTER DIMENSION	9.3 MM
MINIMUM BEND RADIUS	60 MM
MAXIMUM COLOR DEPTH	48-BIT, 16 BITS PER COLOR
MAXIMUM REFRESH RATE	4K 60 HZ + HDR
HDMI HIGH SPEED	YES
ETHERNET	YES
AUDIO RETURN CHANNEL	YES
DEEP COLOR SUPPORT	YES
3D COMPATIBLE	YES
4K SUPPORT	YES
AUDIO SUPPORT	DTS-HD DOLBY TRUEHD, ATMOS

For more information please call 1-833-574-9124 or email [AVARRO@adiglobal.com](mailto:AVARRO@adiglobal.com)

To learn more about AVARRO products visit [avarro.adiglobaldistribution.us](http://avarro.adiglobaldistribution.us)

