

# PROXIMITY CREDENTIALS

## PRE-PROGRAMMED, XSF FORMAT



These proximity credentials are pre-programmed with 26 bit/XSF formatting and available in four models. Our XSF credentials deliver contactless access control with exceptional durability and value.



## FEATURES

Compatible with 125kHz proximity readers programmed for 26 bit XSF format

Durable ABS or PVC construction with passive design (no battery) for long-term use

Conveniently pre-programmed (26 bit XSF)

Always in stock

4-Year Warranty

## Product Specifications

Frequency: 125kHz

Format: 26 bit/XSF

### Quantity:

50-pack: 0E-CLAMXSF50, 0E-ISOXSF50, 0E-KEYXSF50  
25-pack: 0E-XSFTAGP25

PRODUCT #	Features	Dimensions	Weight	Materials	Operating Temp.
0E-CLAMXSF50 Clamshell	Vertical slot	3.37" x 2.125" x 0.075" (8.56 x 5.4 x 0.19cm)	0.317 oz. (9g)	ABS shell PVC label	-50° to 160°F (-45° to 70°C)
0E-ISOXSF50 ISO	Printable No slot	3.37" x 2.125" x 0.033" (8.56 x 5.4 x 0.084cm)	0.212 oz. (6g)	PVC	-50° to 160°F (-45° to 70°C)
0E-KEYXSF50 Keyfob	Attaches to keyring	1.44" x 1.18" x 0.25" (3.66 x 3 x 0.635cm)	0.15 oz. (4.25g)	ABS	-50° to 165°F (-45° to 73°C)
0E-XSFTAGP25 Disc Tag	Adhesive	1.38" x .05" (3.5 x .125cm)	0.045 oz. (1.28g)	PVC with adhesive back	-50° to 160°F (-45° to 70°C)

For more information contact your ADI Sales person or visit [adiglobal.com/adiexclusivebrands](http://adiglobal.com/adiexclusivebrands)