

PROXIMITY CREDENTIALS

PRE-PROGRAMMED, 36 Bit/C15001



These proximity credentials are pre-programmed with 36 Bit/C15001 formatting and available in three models. Our 36 bit credentials deliver contactless access control with exceptional durability and value.



FEATURES

Compatible with 125kHz proximity readers programmed for 36 Bit/C15001 format

Durable ABS or PVC construction with passive design (no battery) for long-term use

Conveniently pre-programmed (36 Bit/C15001 format)

Always in stock

4-Year Warranty

Product Specifications

Frequency: 125kHz

Format: 36 Bit/C15001

Quantity: 50-pack

PRODUCT #	Features	Dimensions	Weight	Materials	Operating Temp.
0E-CLAM36P50 Clamshell	Vertical slot	3.37" x 2.125" x 0.075" (8.56 x 5.4 x 0.19cm)	0.317 oz. (9g)	ABS shell PVC label	-50° to 160°F (-45° to 70°C)
0E-ISO36PK50 ISO	Printable No slot	3.37" x 2.125" x 0.033" (8.56 x 5.4 x 0.084cm)	0.212 oz. (6g)	PVC	-50° to 160°F (-45° to 70°C)
0E-KEY36P50 Keyfob	Attaches to keyring	1.44" x 1.18" x 0.25" (3.66 x 3 x 0.635cm)	0.15 oz. (4.25g)	ABS	-50° to 165°F (-45° to 73°C)

For more information contact your ADI Sales person or visit adiglobal.com/adiexclusivebrands