

## PLUG-IN ADAPTER

**0E-PPS24V2AS**

**24VDC, 2 AMP**

**SCREW TERMINAL WITH GROUND**



The 0E-PPS24V2AS is a fully regulated 24VDC, 2 amp plug-in switching adapter that provides reliable DC power for a wide variety of indoor security and surveillance products and applications. It can be used with input voltage ranging from 100 to 240VAC and includes a power indicator LED. Self-limiting protection against short circuit and overload conditions is included, with auto recovery. Complies with DOE Level VI Efficiency and FCC requirements.

- 24VDC, 2 AMP (48 WATTS)
- PRIMARY: 100 to 240VAC, 50/60Hz, 0.8A
- I.T.E. POWER SUPPLY
- SHORT CIRCUIT AND OVERLOAD PROTECTED;  
AUTO RECOVERING
- POWER INDICATOR LED
- 3 PRONG, 3 SCREW TERMINAL WITH GROUND
- EFFICIENCY LEVEL VI, FCC COMPLIANT; UL LISTED
- FOR INDOOR USE ONLY
- OPERATING TEMP.: 32°F to 113°F (0°C to 45°C)

PART #: 0E-PPS24V2AS

UPC: 811914020097

LENGTH: 1.6"

WIDTH: 2.2"

HEIGHT: 4.3"

WEIGHT: 4.3 OUNCES



**FOR MORE INFORMATION,  
CONTACT YOUR ADI SALES PERSON.**

[wboxtech.com](http://wboxtech.com)