

PROXIMITY CREDENTIALS

PRE-PROGRAMMED, 26 BIT



These proximity credentials are pre-programmed with 26 bit, Wiegand-compatible formatting and are available in four models. Our 26 bit credentials deliver contactless access control with exceptional durability and value.



FEATURES

Compatible with 125kHz proximity readers programmed for 26 bit format (Wiegand-compatible)

Durable ABS or PVC construction with passive design (no battery) for long-term use

Conveniently pre-programmed (26 bit format, Wiegand-compatible)

Always in stock

4-Year Warranty

Product Specifications

Frequency: 125kHz

Format: 26 bit

Quantity: 25-pack

PRODUCT #	Features	Dimensions	Weight	Materials	Operating Temp.
0E-CLAMPK25 Clamshell	Vertical slot	3.37" x 2.125" x 0.075" (8.56 x 5.4 x 0.19cm)	0.317 oz. (9g)	ABS shell PVC label	-50° to 160°F (-45° to 70°C)
0E-ISOPK25 ISO	Printable No slot	3.37" x 2.125" x 0.033" (8.56 x 5.4 x 0.084cm)	0.212 oz. (6g)	PVC	-50° to 160°F (-45° to 70°C)
0E-KEYFPK25 Keyfob	Attaches to keyring	1.44" x 1.18" x 0.25" (3.66 x 3 x 0.635cm)	0.15 oz. (4.25g)	ABS	-50° to 165°F (-45° to 73°C)
0E-PXTAGPK25 Disc Tag	Adhesive	1.38" x .05" (3.5 x .125cm)	0.045 oz. (1.28g)	PVC with adhesive back	-50° to 160°F (-45° to 70°C)

For more information contact your ADI Sales person or visit adiglobal.com/adiexclusivebrands