

VGA CONVERTER

VGA TO BNC/VIDEO

ADI
PRO

Connect a DVR with VGA output to an existing monitor with BNC input. This VGA Converter includes dual composite S-Video, BNC and VGA output ports, as well as a USB power supply (5VDC). NTSC/PAL video standards are supported, with a maximum resolution of 2560x1600. Auto configuration is available for resolutions up to 1024x768 (up to 75Hz), and an on-screen display (OSD) allows for easy adjustments to image size, brightness, contrast, hue, saturation, sharpness and more.



FEATURES

One VGA input, one VGA output

One BNC output, one S-Video output

One USB power supply (5VDC)

Simultaneous output to VGA/Video/S-Video signals

Display simultaneous pictures on monitor and TV

Supports OVERSCAN and UNDERSCAN display mode

Supports PC and MAC computers

Limited Lifetime Warranty

Product Specifications

SINGLE ITEM

PART # 0E-VGABNC

DIMENSIONS:

4.33"/110mm L x 2.20"/56mm W x
1.42"/36mm H

COLOR: Black



**For more information contact
your ADI Sales person or visit
adiglobal.com/adiexclusivebrands**