

PROXIMITY CREDENTIALS

PRE-PROGRAMMED, XSF FORMAT



These proximity credentials are pre-programmed with 26 bit/XSF formatting and available in four models. Our XSF credentials deliver contactless access control with exceptional durability and value.



FEATURES

Compatible with 125kHz proximity readers programmed for 26 bit XSF format

Durable ABS or PVC construction with passive design (no battery) for long-term use

Conveniently pre-programmed (26 bit XSF)

Always in stock

4-Year Warranty

Product Specifications

Frequency: 125kHz

Format: 26 bit/XSF

Quantity:

50-pack: 0E-CLAMXSF50, 0E-ISOXSF50, 0E-KEYXSF50
25-pack: 0E-XSFTAGP25

PRODUCT #	Features	Dimensions	Weight	Materials	Operating Temp.
0E-CLAMXSF50 Clamshell	Vertical slot	3.37" x 2.125" x 0.075" (8.56 x 5.4 x 0.19cm)	0.317 oz. (9g)	ABS shell PVC label	-50° to 160°F (-45° to 70°C)
0E-ISOXSF50 ISO	Printable No slot	3.37" x 2.125" x 0.033" (8.56 x 5.4 x 0.084cm)	0.212 oz. (6g)	PVC	-50° to 160°F (-45° to 70°C)
0E-KEYXSF50 Keyfob	Attaches to keyring	1.44" x 1.18" x 0.25" (3.66 x 3 x 0.635cm)	0.15 oz. (4.25g)	ABS	-50° to 165°F (-45° to 73°C)
0E-XSFTAGP25 Disc Tag	Adhesive	1.38" x .05" (3.5 x .125cm)	0.045 oz. (1.28g)	PVC with adhesive back	-50° to 160°F (-45° to 70°C)

For more information contact your ADI Sales person or visit adiglobal.com/adiexclusivebrands