

SELF-CONTAINED OUTDOOR SIREN

0E-OUTDSIREN
SELF-CONTAINED, HIGH POWER SIREN
TAMPER SWITCH PROTECTED



High output self-contained siren system (also available with strobe). Loud 120dB warble tone siren in vandal and weather resistant polycarbonate housing. Sturdy aluminum back plate and tamper switch.

- WARBLE TONE SIREN
- SOLID ALUMINUM BACK PLATE
- HIGH OUTPUT 120 DB (1W/1M)
- 6-14VDC
- VANDAL AND WEATHER RESISTANT
- INDOOR/OUTDOOR
- MOUNTS TO 4" ELECTRICAL BOX

PART #: 0E-OUTDSIREN
UPC: 811914020783
LENGTH: 4.63"
WIDTH: 5.5"
HEIGHT: 4.28"
WEIGHT: 1 LB, 12 OUNCES