

## HIGH POWER COMPACT SIREN

**0E-30WCSIREN**  
**30 WATT, DUAL TONE**  
**WEATHER RESISTANT**



Patented piezo dynamic technology creates loud 119dB output with minimal size, weight and current draw (390mA @ 12V). Two tones: steady or yelp. Includes mounting bracket. Mount and 5" X 8" siren fit standard siren box.

- PATENTED PIEZO DYNAMIC TECHNOLOGY
- 119 DB (1W/iM)
- 2 TONES: STEADY OR YELP
- LOW 390MA CURRENT DRAW
- INDOOR/OUTDOOR
- HIGH IMPACT ABS PLASTIC
- WEATHER RESISTANT
- WHITE

PART #: 0E-30WCSIREN

UPC: 811914020011

LENGTH: 4"

WIDTH: 5.25"

HEIGHT: 5.5"

WEIGHT: 6.2 OUNCES